



40 West Illiana Street Orlando, FL 32806
Phone: 407-839-6213 Fax: 407-367-0695
Toll Free: 888-839-6213
www.evoii.com

STOCK ORDER FORM

SHIP TO:			BILL TO:		
COMPANY:			COMPANY:		
ADDRESS:			ADDRESS:		
ADDRESS:			ADDRESS:		
CITY:	STATE:	ZIP:	CITY:	STATE:	ZIP:
PHONE:	FAX:		PHONE:	FAX:	

PO #: **SHIPPING (via UPS) Circle Priority: NEXT DAY AIR 2ND DAY 3RD DAY GROUND**

Aura Socks

Item	Description	Quantity
SSN-1.5-10-3	Aura sealing sock size 1 1/2, 10" long w/ seal 3" from distal	
SSN-2-10-4	Aura sealing sock size 2, 10" long w/ seal 4" from distal	
SSN-2.5-10-4	Aura sealing sock size 2 1/2, 10" long w/ seal 4" from distal	
SSN-3-12-5	Aura sealing sock size 3, 12" long w/ seal 5" from distal	
SSN-3.5-12-5	Aura sealing sock size 3 1/2, 12" long w/ seal 5" from distal	
SSN-4-12-5.5	Aura sealing sock size 4, 12" long w/ seal 5.5" from distal	
SSN-4.5-14-6	Aura sealing sock size 4 1/2, 14" long w/ seal 6" from distal	
SSN-5-14-6	Aura sealing sock size 5, 14" long w/ seal 6" from distal	
SSN-6-16-6	Aura sealing sock size 6, 16" long w/ seal 6" from distal	
SSN-7-16-6	Aura sealing sock size 7, 16" long w/ seal 6" from distal	
SSN-8-18-6	Aura sealing sock size 8, 18" long w/ seal 6" from distal	
SSN-9-20-7	Aura sealing sock size 9, 16" long w/ seal 7" from distal	

Fabrication Supplies

Item	Description	Quantity
VAP-001	AK alignment plates	
VAP-002	BK alignment plates	
VHP-001	Vacuum hand pump red handles	
VLC-100	Stainless steel one way valve	
VLC-101	Straight stainless steel 10/32 to 1/8" barb	
VLC-102	90 degree stainless steel 10/32 to 1/8" barb	
VLC-102A	45 degree 10/32 to 1/8" barb	
VLC-102B	90 degree s/s adjustable barb	
VLC-103	Tygon tubing -3603 1/8IDx1/4OD per foot	
VLC-310	Push pin - quick release	
VLC-400V	V5 expulsion valve kit	
VLM-001	PETG 1/8" cut 16" x 16"	
VLM-002	PETG 3/8" cut 16" x 16"	
VLM-003	PETG 1/2" cut 16" x 16"	
VLM-101	5" carbon fiber braid sleeving (per pound)	
VLM-102	8" carbon fiber braid sleeving (per pound)	
VLM-201	Fiberglass braid 5" (per pound)	
VLM-202	Fiberglass braid 9" (per pound)	
VLS-004	Expulsion valve pump adapter	
VMP-001	Universal mounting plate (low profile)	
VMP-002	Universal mounting plate (heavy duty)	
VMP-004	Mounting plate lamination dummy	
VMP-006	Mounting plate for ossur lock	
VMP-007	Valve plate	
VMP-008	Mounting plate for fillauer plate	
VMP-009	Offset fillauer mounting plate	

Fabrication Supplies

Item	Description	Quantity
VSPC-001	Seal plate one way valve	
VV03-001	Velocity expulsion valve housing	
VV03-002	Velocity valve lamination dummy	
VV03-003	Replacement duckbill valve	
VV03-004	Velocity vacuum valve housing	
VV03-LLS	Limblologic seal	
WT-001	Wrench	
EVP-001	Electronic vacuum pump	
PVV01-001	Pediatric velocity valve starter kit	
PVV01-002	Pediatric expulsion valve kit	
PVMP-001	Pediatric mounting plate (anodized purple)	
PVMP-004	Pediatric mounting plate lamination dummy	
PVMP-007	Pediatric valve mounting plate	
PVV03-001	Pediatric expulsion valve housing - black	
PVV03-002	Pediatric valve lamination dummy	
PVV03-003	Pediatric replacement duckbill valve	
VLC-143	Proximal lateral lanyard attachment screw	
VLC-312	Side pin housing and quick release pin kit	
VSP-001	Velocity seal plate	
VSP-002	Velocity seal plate with release valve	
VSPC-002	Seal plate release valve kit	
VV01-001	Velocity valve starter kit	
VV01-002	Velocity expulsion valve kit	
VV01-003	Velocity vacuum valve kit	
VV01-004	AK expulsion valve kit	
VV01-005	AK vacuum valve kit	
VV02-001	Velocity expulsion valve & housing	
VV02-002	Velocity vacuum valve & housing	
VV02-003	Aluminum vacuum housing & valve	
VV03-005	AK lamination valve housing (blue)	
VV03-006	Aluminum vacuum valve housing (orange)	
VV04-001	Velocity vacuum valve spacer plate	

Spots

Item	Description	Quantity
VSS-001	Silicone V spot size 1	
VSS-002	Silicone V spot size 2	
VSS-003	Silicone V spot size 3	
VUS-001	Urethane V spot size 1	
VUS-002	Urethane V spot size 2	
VUS-003	Urethane V spot size 3	
VUS-101	Urethane V spot size 1 with cover	
VUS-102	Urethane V spot size 2 with cover	
VUS-103	Urethane V spot size 3 with cover	

Urethane spots are used for extra cushioning in laminations, fibula head, distal tibia. Gorilla urethane glue is recommended as an adhesive. Silicone spots are used for volume management. There is no adhesive for silicone.

NOTES: _____

Carbon and fiberglass are bought and sold by the pound. According to the manufacturer, the material length can vary depending on how tight it is stretched. The average length per pound for each material is listed below.

Carbon Fiber 5.0 dia.	7.6 ft/pound	Fiberglass 5.0 dia.	11.4 ft/pound
Carbon Fiber 8.0 dia.	4.8 ft/pound	Fiberglass 9.0 dia.	6.4 ft/pound